Signetics

TDA3047 IR Preamplifier

Product Specification

Linear Products

DESCRIPTION

The TDA3047 is for infrared reception with low power consumption.

FEATURES

- HF amplifier with a control range of 66dB
- Synchronous demodulator and reference amplifier
- AGC detector
- Pulse shaper
- Q-factor killing of the input selectivity, which is controlled by the AGC circuit
- Input voltage limiter

APPLICATION

• IR remote control systems


PIN CONFIGURATION



ORDERING INFORMATION

DESCRIPTION	TEMPERATURE RANGE	ORDER CODE
16-Pin Plastic DIP (SOT-38)	-25°C to +125°C	TDA3047N
16-Pin Plastic SO (SOT-109A)	0 to +70°C	TDA3047TD

BLOCK DIAGRAM



IR Preamplifier

TDA3047

ABSOLUTE MAXIMUM RATINGS

SYMBOL	PARAMETER	RATING	V	
Vcc	Supply voltage (Pin 8)	13.2		
111	Output current pulse shaper (Pin 11)	10		
V ₂₋₁₅ V ₄₋₁₃ V ₅₋₆ V ₇₋₁₀ V ₉₋₁₁	V ₄₋₁₃ Pins 4 and 13 4.5 V ₅₋₆ Pins 5 and 6 4.5 V ₇₋₁₀ Pins 7 and 10 4.5		V V V	
T _{STG}	Storage temperature range	-65 to +150	°C	
TA	Operating ambient temperature range	-25 to +125	°C	

NOTE:

DC ELECTRICAL CHARACTERISTICS $V_{CC} = V_8 = 5V$; $T_A = 25^{\circ}C$, measured in Figure 3, unless otherwise specified.

	PARAMETER	LIMITS			
SYMBOL		Min	Тур	Max	UNIT
Supply (Pin 8)					
V _{CC}	Supply voltage	4.65	5.0	5.35	V
I _{CC} = I ₈	Supply current	1.2	2.1	3.0	mA
Controlled HF	amplifier (Pins 2 and 15)				
V _{2 - 15(P-P)} V _{2 - 15(P-P)}	Minimum input signal (peak-to-peak value) at f = 36kHz ¹ at f = 36kHz ²		15	25 5	μV μV
	AGC control range (without Q-killing)	60	66		dB
V _{2 - 15(P-P)}	Input signal for correct operation (peak-to-peak value)3	0.02		200	mV
V _{2 - 15(P-P)}	Q-killing inactive ($I_9 = I_{14} < 0.5 \mu A$) peak-to-peak value)			140	μ۷
V _{2-15(P-P)}	Q-killing active (I ₁₄ = I ₃ = max.) (peak-to-peak value)	28			mV
	Q-killing range	Figure 1			
Inputs					
V ₂	Input voltage (Pin 2)	2.25	2.45	2.65	V
V ₁₅	Input voltage (Pin 15)	2.25	2.45	2.65	V
R ₂₋₁₅	Input resistance (Pin 2)	10	15	20	kΩ
C ₂₋₁₅	Input capacitance (Pin 2)		3		pF
V _{1 - 16}	Input limiting (Pin 1) at I ₁ = 3mA		0.8	0.9	٧
Outputs					
-V ₉₋₈	Output voltage HIGH (Pin 9) at -I ₉ = 75μA		0.1	0.5	V
V ₉	Output voltage LOW (Pin 9) at I ₉ = 75μA		0.1	0.5	V
-l9 -l9 -l9	Output current; output voltage HIGH at V_9 = 4.5V at V_9 = 3.0V at V_9 = 1.0V	75 75 75	120 130 140		μΑ μΑ μΑ
l ₉	Output current; output voltage LOW at V ₉ = 0.5V	75	120		μА
R ₇₋₁₀	Output resistance between Pins 7 and 10	3.1	4.7	6.2	kΩ

March 2, 1987 5-53

^{1.} All pins except Pin 11 are short-circuit protected.

Signetics Linear Products Product Specification

IR Preamplifier

TDA3047

DC ELECTRICAL CHARACTERISTICS (Continued) V_{CC} = V₈ = 5V; T_A = 25°C, measured in Figure 3, unless otherwise specified.

SYMBOL	PARAMETER	LIMITS			
		Min	Тур	Max	UNIT
Pulse shaper (Pin 11)		<u></u>		
V ₁₁	Trigger level in positive direction (voltage Pin 9 changes from HIGH to LOW)	3.75	3.9	4.05	v
V ₁₁	Trigger level in negative direction (voltage Pin 9 changes from LOW to HIGH)	3.4	3.55	3.7	v
ΔV ₁₁	Hysteresis of trigger levels	0.25	0.35	0.45	V
AGC detector	(Pin 12)	•	•		•
-112	AGC capacitor charge current	3.3	4.7	6.1	μА
12	AGC capacitor discharge current	67	100	133	μΑ
Q-factor killer	(Pins 3 and 14)	. •	•	•	•
-l ₃	Output current (Pin 3) at V ₁₂₋₁₆ = 2V	2.5	7.5	15	μА
-114	Output current (Pin 14) at V ₁₂₋₁₆ = 2V	2.5	7.5	15	μА

NOTES:

- 1. Voltage Pin 9 is HIGH; $-l_9 = 75\mu$ A.
- 2. Voltage Pin 9 remains LOW.
- 3. Undistorted output pulse with 100% AM input.

FUNCTIONAL DESCRIPTION

General

The circuit operates from a 5V supply and has a current consumption of 2mA. The output is a current source which can drive or suppress current of > 75µA with a voltage swing of 4.5V. The Q-killer circuit eliminates distortion of the output pulses due to the decay of the tuned input circuit at high input voltages. The input circuit is protected against signals of > 600mV by an input limiter. The typical input is an AM signal at a frequency of 36kHz. Figures 2 and 3 show the circuit diagrams for the application of narrow-band and wide-band receivers, respectively. Circuit description of the eight sections shown in the Block Diagram are given below.

Controlled HF Amplifier

The input signal is amplified by the gain-controlled amplifier. This circuit comprises three DC amplifier stages connected in cascade. The overall gain of the circuit is approximately 83dB and the gain control range is in the order of 66dB. Gain control is initially active in the second amplifier stage and is transferred to the first stage as limiting in the second stage occurs, thus maintaining optimum signal-to-noise ratio. Offset voltages in the DC coupled amplifier are minimized by two negative feedback loops. These also allow the circuit to have some series resis-

tance of the decoupling capacitor. The output signal of the amplifier is applied to the reference amplifier and to the synchronous demodulator inputs.

Reference Amplifier

The reference amplifier amplifies and limits the input signal. The voltage gain is approximately 0dB. The output signal of this amplifier is applied to the synchronous demodulator.

Synchronous Demodulator

In the synchronous demodulator, the input signal and reference signal are multiplied. The demodulator output current is $25\mu\mathrm{A}$ peak-to-peak. The output signal of the demodulator is fed to the input of the AGC detector and to the input of the pulse-shaper circuit.

AGC Detector

The AGC detector comprises two NPN transistors operating as a differential pair. The top level of the output signal from the synchronous demodulator is detected by the AGC circuit. Noise pulses are integrated by an internal capacitor. The output signal is amplified and applied to the first and second stages of the amplifier and to the Q-factor killer circuit.

Pulse-Shaper

The pulse-shaper comprises two NPN transistors operating as a differential pair con-

nected in parallel with the AGC differential pair. The slicing level of the pulse shaper is lower than the slicing level of the AGC detector. The output of the pulse-shaper is determined by the voltage of the capacitor connected to Pin 11 which is applied directly to the output buffer.

Output Buffer

The voltage of the pulse-shaper capacitor is fed to the base of the first transistor of a differential pair. To obtain a correct RC-5 code, a hysteresis circuit protects the output against spikes. The output at Pin 9 is active HIGH.

Q-factor Killer

Figure 2 shows the Q-factor killer in the narrow-band application. In this application it is necessary to decrease the Q-factor of the input selectivity particularly when large input signals occur at Pins 2 and 15. In the narrow-band application the output of the Q-factor killer can be directly coupled to the input; Pin 3 to Pin 2, and Pin 14 to Pin 15.


Input Limiter

In the narrow-band application, high voltage peaks can occur on the input of the selectivity circuit. The input limiter limits these voltage peaks to approximately 0.7V. Limiting is 0.9V maximum at 1, = 3mA.

March 2, 1987 5-54

IR Preamplifier

TDA3047



Function of the Peak-to-Peak Input Voltage (V₂-15)

