


**AXIAL** 

Weight = 0.4 g

Marking: clear, ring at cathode end

Cooling methode: by convertion (method A)



	DIMENSIONS			
REF.	Millimeters		Inches	
	Min.	Max.	Min.	Max.
А	6.05	6.35	0.238	0.250
В	26		1.024	
ØC	2.95	3.05	0.116	0.120
ØD	0.76	0.86	0.029	0.034
Е		1.27		0.050

## **NOTES**

- 1 The lead diameter Ø D is not controlled over zone E
- 2 The minimum axial lengh within which the device may be placed with its leads bent at right angles is 0.59"(15 mm)

